



ISOMETRIC VIEW SCALE 1:2

STANDARD TOLERANCES	
<6	±0.2
>6 <18	±0.3
>18 <30	±0.4
>30 <50	±0.5
>50 <80	±0.6
>80 <120	±0.7
>120 <180	±0.8
>180 <250	±1.0
>250 <315	±1.2
>315 <400	±1.5
>400 <500	±1.8

COMPONENTS				
Nr.	DESIGNATION	REFERENCE	QTY.	RAW MATERIAL
1	Cristal Glass SM TLK	300610	1 Un.	Cristal PMMA
2	Cable housing SM TLK	101417	1 Un.	Black ABS
3	LED plate BETA/SM TLK 12v0,28w/24v0,9w	LP0062	1 Un.	-
4	OPEN CABLE ADR (TU . EEG . 52 - 01) SM TLK	0.5mt - C10320 1.5mt - C10321 5.0mt - C10337	1 Un.	-
5	Resin SIKA Melt	300518	4 Gr.	-

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS
SURFACE FINISH:
TOLERANCES:
LINEAR:
ANGULAR:

FINISH:
DEBUR AND
BREAK SHARP
EDGES

DO NOT SCALE DRAWING
REVISION 0
TEKL S. A.

NAME	SIGNATURE	DATE			
DRAWN	TS	04/08/2010			
CHK'D	MC	04/08/2010			
APP'V'D	CR	04/08/2010			
MFG					
Q.A					
			MATERIAL:		
			WEIGHT:		

TITLE:
FRONT MARKER TLK CRISTAL
(Open cable)

DWG NO.	0. 5mt FR2454 / TM098230420 (ERMAX)	A4
	1. 5mt FR2455 / TM098230425 (ERMAX)	
	5. 0mt FR2456 / TM098230427 (ERMAX)	

SCALE: 1:1
SHEET 1 OF 1