

Coupler connector - ST-17P1N8A9K04S - 1614532

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Coupler connector, straight, SPEEDCON locking, M17, Number of positions: 17, Type of contact: Male connector, Crimp connection, shielded: Yes, Cable diameter: 9 mm...11 mm

The figure shows the 8-pos. product version

Key commercial data

package_quantity	1
GTIN	4046356708746

Technical data

General

Note	Order information Order crimp contacts Ø 0.6 mm separately
Type of locking	SPEEDCON locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Male connector
Number of positions	17
Nominal current per power contact at 25°C	3.6 A
Conductor entry	9 mm ... 11 mm

Ambient conditions

Degree of protection	IP67
----------------------	------

Specifications according to DIN EN 61984:2001

Installation height max.	3000 m
Nominal / operating voltage of power contacts	60 V
Rated surge voltage of power contacts	1.5 kV
Surge voltage category of power contacts	II
Pollution degree of power contacts	3

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701

Coupler connector - ST-17P1N8A9K04S - 1614532

classifications

eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440102

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002635
ETIM 5.0	EC002635

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

approvals

UL Recognized / UL Recognized / cUL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized	
Nominal voltage UN	60 V
Nominal current IN	1 A
mm ² /AWG/kcmil	0.14-0.6

Nominal voltage UN	60 V
Nominal current IN	1 A
mm ² /AWG/kcmil	0.14-0.6

cUL Recognized	
-----------------------	--

Coupler connector - ST-17P1N8A9K04S - 1614532

approvals

Nominal voltage UN	60 V
Nominal current IN	1 A
mm ² /AWG/kcmil	0.14-0.6

Nominal voltage UN	60 V
Nominal current IN	1 A
mm ² /AWG/kcmil	0.14-0.6

cULus Recognized	
------------------	--

accessories

Crimp contact

ST-06KP010 - 1607577



ST-06KP020 - 1607578



ST-06KP030 - 1607579



Protective cover

Coupler connector - ST-17P1N8A9K04S - 1614532

accessories

ST-Z0006 - 1607776




Mounting material

ST-Z0001 - 1607770



Drawings

Dimensioned drawing



Coupler connector - ST-17P1N8A9K04S - 1614532

Schematic diagram

