

Light Sensing Applications

Photocells M 9960

small Photocell
epoxy encapsulated housing


Beacon Light Applications

Photometer Applications


With this range we offer two selections of a small flat design photocell with low light resistance.

Operating Temperature Range: -20...+70 °C (non continuous)

Storage Temperature Range: -20...+80 °C (non continuous)



Type	R ₁₀	R ₁₀₀	R ₀₁	R ₀₅	V _{max}	P _{max}	γ _{10/100}	λ _{peak}
units	KΩ	KΩ typ.	MΩ min	MΩ min	V	mW	typ.	nm
M9960 11a	1,5...5,0	0,7	0,05	0,15	100	200	0,7	600
M9960 11b	0,8...2,0	0,4	0,05	0,15	100	200	0,65	600



Europe:
PerkinElmer Optoelectronics
GmbH & CoKG
Wenzel Jaksch Str 31
65199 Wiesbaden / Germany
Phone +49(0)611 492 0
Fax +49(0)611 492 170

USA:
PerkinElmer Optoelectronics
44370 Christy Street
Freemont, CA 94538-3180
Phone +510 979 6500
+800 775 6786
Fax +510 687 1140

Asia:
PerkinElmer Optoelectronics
47, Ayer Rajah Crescent #06-12
Singapore 139947
Phone +65 775 2022
Fax +65 775 1008



Right for modification reserved / WS / 28.8.2003