

Starter Set Climate Control

Product ref.: 142546A0



Product features

- Demand-based and comfortable heating control via free smartphone app
- Individual control of your personal comfort temperature in each room
- The Access Point connects the smartphone via the Homematic IP cloud with all Homematic IP devices
- The Radiator Thermostat replaces conventional thermostats and regulates the room temperature according to the individual needs of the user
- The Window / Door Contact detects opening and closing of windows and automatically turns down the heating
- Reliable HmIP radio protocol based on 868 MHz
- High security thanks to comprehensive AES encryption and server location in Germany - requires no personal data

Technical specifications

Access Point:	
Supply voltage	Power supply unit (5 V)
Dimensions (W x H x D)	118 x 104 x 26 mm
Typ. open area RF range	400 m
Radiator Thermostat:	
Supply voltage	2x 1.5 V LR6/mignon/AA
Battery life	2 years (typ.)
Dimensions (W x H x D)	58 x 71 x 97 mm
Typ. open area RF range	300 m
Window / Door Contact:	
Supply voltage	1x 1.5 V LR03/micro/AAA
Battery life	2 years (typ.)
Dimensions (W x H x D)	102 x 15 x 20 mm
Typ. open area RF range	300 m

Logistical data

Product reference	142546A0
EAN code	4047976425464
Short description	HmIP-SK1
Packing unit	6
Packing dimensions	325 x 159 x 106 mm

Package contents

Home Control Access Point (plug-in mains adapter, network cable)
Radiator Thermostat (adapter Danfoss RA, RAV and RAVL, support ring)
Window / Door Contact - optical (caps in white and brown)
Batteries
Mounting accessories
User manuals