



Vergleichstabelle

	Artikelnr.: 1420551	Artikelnr.: 1365375
Standard	WiVu	WiVu
compress	H.264	H.264
Photo		
Processor	CAVIUM CNW8302	CAVIUM CNW8302
Resolution	1080p/60	1080p/60
Frequency	WiFi 5GHz band	WiFi 5GHz band
Latency	500ms (less than 300ms)	500ms (less than 300ms)
Housing	Plastic + aluminum	Plastic
	Bigger dimension	smaller dimension
	Bigger heat-sink	smaller heat-sink
Transmission / reception system	External High gain dual Antenna (5dBi) x 4 pcs	Internal PCB Antenna (0dBi)
	Golden-planted high efficiency 5G conducting kit x 4 sets	Non
Transmission Distance L.O.S.	>100 M	30M
Transmission through wall (concrete wall)	Best	Good
HDMI input	1	1
Loop Through	Yes	Yes
IR control band (Blaster/Sensor)	Support full range 30~60KHz. Highly compatible with most of home appliance.	Support full range 30~60KHz. Highly compatible with most of home appliance.
Power Supply	DC 5V/1A micro USB (Low power consumption)	DC 5V/1A micro USB (Low power consumption)