



Color	:	BLUE
Wavelength/color Temperature	:	typ. 465-475Nm
Length	:	56cm
Width	:	1cm
Number of LEDs	:	40
Brightness(mcd)	:	400-500
Viewing angle	:	110°
Voltage	:	max. 24V/DC
Fixing	:	"3M" tape