



Color	:	GREEN
Wavelength/color Temperature	:	typ. 520-530Nm
Length	:	56cm
Width	:	1cm
Number of LEDs	:	40
Brightness(mcd)	:	700-900
Viewing angle	:	110°
Voltage	:	max. 24V/DC
Fixing	:	"3M" tape