

## Crimp Sleeves for DCRP Series

## TECHNICAL SPECIFICATIONS

Material: Brass, Nickel Plated

Operating Temperature: -40°C to +120°C



## Ordering information:

Name:	P/N :	Product Code:	Info:
Crimp Sleeve	1599-0011-01	CS 9-50	5,0 - 6,0 mm
Crimp Sleeve	1599-0011-02	CS 9-50	5,5 - 6,5 mm
Crimp Sleeve	1599-0011-03	CS 9-50	6,0 - 7,0 mm
Crimp Sleeve	1599-0011-04	CS 9-50	6,5 - 7,5 mm
Crimp Sleeve	1599-0011-05	CS 9-50	7,0 - 8,0 mm
Crimp Sleeve	1599-0011-06	CS 9-50	7,5 - 8,5 mm
Crimp Sleeve	1599-0011-07	CS 9-50	8,0 - 9,0 mm
Crimp Sleeve	1599-0011-08	CS 9-50	8,5 - 9,5 mm
Crimp Sleeve	1599-0011-09	CS 9-50	9,0 - 10,0 mm
Crimp Sleeve	1599-0011-10	CS 9-50	9,5 - 10,5 mm
Crimp Sleeve	1599-0011-11	CS 9-50	10,0 - 11,0 mm
Crimp Sleeve	1599-0011-12	CS 9-50	10,5 - 11,5 mm
Crimp Sleeve	1599-0011-13	CS 9-50	11,0 - 12,0 mm
Crimp Sleeve	1599-0011-14	CS 9-50	11,5 - 12,5 mm
Crimp Sleeve	1599-0011-15	CS 9-50	12,0 - 13,0 mm
Crimp Sleeve	1599-0011-16	CS 9-50	12,5 - 13,5 mm
Crimp Sleeve	1599-0011-17	CS 9-50	13,0 - 14,0 mm
Crimp Sleeve	1599-0011-18	CS 9-50	13,7 - 15,0 mm
Crimp Sleeve	1599-0011-19	CS 9-50	14,0 - 15,0 mm
Crimp Sleeve	1599-0011-20	CS 9-50	14,5 - 15,5 mm
Crimp Sleeve	1599-0011-21	CS 9-50	16,0 - 17,0 mm

