



REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 05/24/05*		

1. PRODUCTS PERFORMANCE:
- 1.0 VOLTAGE RATING: 250V AC.
 - 1.1 CONTACT CURRENT RATING: 1.5A MAX. PER PIN.
 - 1.2 CONTACT RESISTANCE: 20 MILLIOHMS MAX.
 - 1.3 DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
 - 1.4 INSULATION RESISTANCE: 1000 MEGOHMS MINI.
 - 1.5 OPERATING TEMPERATURE: -20°C~+70°C.
2. PRODUCT NUMBER CODE:



DS1043 - X XXX X

ROW Spacing
 0: 0.3 and 0.6mm
 3: 0.3 inch(7.62mm)
 4: 0.4 inch(10.16mm)
 6: 0.6 inch(15.24mm)
 9: 0.9 inch(22.86mm)

Number of leads:
 24\28\32\40\48

Contact plating:
 T: TIN
 S1: Gold Flash

Option:
 00: Blue 01:Black 07:Green

Series NO.:
 DS1043

GENERAL TOLERANCE		ANGLE TOLERANCE	
X, ±0.60	X, ±5°	X, ±0.38	X, ±1°
XX, ±0.25	XX, ±2°		
DRAWING TYPE	CUSTOMER	SHEET	1 OF 1
SCALE	1:1		
DRAWING NO.	C-DS1043-xxxxx		

PROJECTION	TITLE
UNITS	ZIF SOCKET
SHEET SIZE	
A4	
SERIES	ZIF SERIES

ZHEN QIN
 NINGBO ZHENQIN ELECTRONIC CO., LTD

宁波正青电子有限公司