

SAIL-VSA-M8G-3-10U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



This valve plug has a transparent housing with an integral seal. The connection cross-section corresponds to 0.5 mm² and can therefore be connected directly to our SAI IDC distributor. The operating status of the valve plug is indicated by an LED. All the valve plugs have a protective circuit. The Weidmüller range of products comprises valve plugs type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection.

General ordering data

Type	SAIL-VSA-M8G-3-10U
Order No.	1099761000
Version	Valve plug, A
GTIN (EAN)	4032248874712
Qty.	1 pc(s).

SAIL-VSA-M8G-3-10U

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	311 g
------------	-------

Technical specifications for cable

No. of poles	3	Core cross-section	0.34 mm ²
Sheath material	PUR	Sheathing colour	Black
Cable length	10 m		

General technical data

Coding	Design A (18 mm), M8 = none	Protection degree	IP 67 (when screwed in)
Contact surface	tinned	LED	Yes
Rated voltage	24 V	Rated current	4 A
Temperature range of housing	-25...+80 °C		

Classifications

eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
------------	-------------	------------	-------------

Approvals

Approvals	
ROHS	Conform