



Type: **57069** **Systems to charge:** **Ni-MH**
Designation:..... **Mini Travel Foldable Plug charger** **Cell sizes:**..... AAA, AA
Cell Configurations:..... AAA, AA, 1 - 2 pcs.

Dimensions: **Charger:**

Lenght:..... 110 ± 1 mm
Widht:..... 50.5 ± 1 mm
Height:..... 82 ± 1 mm
Weight:..... 90 ± 3 g

Charging methods: **AC plug in Charge:** **Maintenance Charge:**

AA:..... Current: 300 mA ±45 mA 1/2 AA Current: 20-100 mA
AAA:..... Current: 150 mA ±25 mA 1/2 AAA Current: 20-100 mA

Housing:

Housing Material:..... ABS
Upper Casing color:..... Silver painting
Lower casing color:..... Black

Indications:

AAA, AA, cell mix:..... Green LED flashing = Charge
AAA, AA, cell mix:..... Green LED fixed = Trickle charge
AAA ,AA, cell mix:..... Green LED off = fault mode

Protective Functions:

AC/DC-Adapter:..... N/A

Power:

Primary:..... 100-240 VAC 50/60 Hz
Secondary:..... 1.4V DC

Cut off criteria:

Ni-MH standard cells:... Timer: 800 mins ± 10% for AA, : 660mins ± 10% for AAA
dV (Delta V): 0-15mV
Vmax: 1.65 ± 0.08V

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries