

**SAIE-7/8"S-4-0.2U-H****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

|            |  |
|------------|--|
| Type       | SAIE-7/8"S-4-0.2U-H                          |
| Order No.  | <a href="#">1292420000</a>                   |
| Version    | Built-in plugs, 7/8", No. of poles: 4, 0.2 m |
| GTIN (EAN) | 4050118088441                                |
| Qty.       | 1 pc(s).                                     |

## SAIE-7/8"S-4-0.2U-H

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 70 g

### General data

|                              |                                    |                     |                      |
|------------------------------|------------------------------------|---------------------|----------------------|
| Cable length                 | 0.2 m                              | Conductor O.D.      | -                    |
| Contact material             | CuZn                               | Contact surface     | Gold-plated          |
| Contact tube diameter        | 7/8"                               | Core cross-section  | 0.75 mm <sup>2</sup> |
| Housing main material        | Zinc diecast, nickel-plated        | Material            | PUR/ PUR             |
| No. of poles                 | 4                                  | Plugging cycles     | ≥ 100                |
| Protection degree            | IP 67                              | Rated current       | 8 A                  |
| Rated current                | 8 A (4- and 5-pole), 10 A (3-pole) | Rated voltage       | 300 V                |
| Rated voltage (text)         | 300 V                              | Strand cable length | 0.2 m                |
| Temperature range of housing | -25...+85 °C                       | Type of connection  | Pin                  |

### Classifications

eClass 6.2 27-26-07-02 eClass 7.1 27-44-01-02

### Approvals

Approvals



ROHS Conform

**SAIE-7/8"S-4-0.2U-H****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

[www.weidmueller.com](http://www.weidmueller.com)**Zeichnungen**