

**Conductor markers
CLI C 1-3 GE/SW Å MP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



CLI C conductor markers are mounted on unconnected conductors. Four different sizes are available for labelling conductor cross-sections from 0.5 mm² to max. 70 mm². The markers are already printed and ready for use. Individual labelling is possible by combining the individual markers.

- Closed markers, reliable and for mounting on unconnected cables
- A special flexible bellow profile ensures a wide application range
- Fast and easy to fit – with minimal effort
- Corresponding accessories make labelling easy
- Permanent, high-quality labelling
- High contrast for optimum legibility

General ordering data

| | |
|------------|---|
| Type | CLI C 1-3 GE/SW Å MP |
| Order No. | 0252611699 |
| Version | Conductor markers, 3 x 4.2 mm, PVC, soft, without Cadmium, Colour: Yellow |
| GTIN (EAN) | 4032248443925 |
| Qty. | 200 pc(s). |

Conductor markers CLI C 1-3 GE/SW Å MP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-------|--------|
| Length | 3 mm | Width | 4.2 mm |
| Height | 5.1 mm | Depth | 5 mm |
| Net weight | 0.065 g | | |

General data

| | | | |
|--|--------------------|-----------------------------------|----------------------------|
| Colour | Yellow | Colour of printing | Black |
| Insulation cross-section, max. | 5 mm | Material | PVC, soft, without Cadmium |
| Material colour according to resistance code | 4 | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Orientation of print | horizontal |
| Printed characters | Upper-case letters | Printing | Å |
| Printing method | Laser print | Recommended industries | Process, Machinery |
| Type of printing | Standard | UL 94 flammability rating | V-0 |

Conductor and cable markers

| | | | |
|-------------------------------|---------------------|----------------------|------|
| Conductor O.D., max. | 5 mm | Conductor O.D., min. | 3 mm |
| Conductor cross-section, min. | 1.5 mm ² | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001530 | UNSPSC | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 | | |

Approvals

| | |
|-----------|---------|
| Approvals | |
| ROHS | Conform |

Datenblatt

**Conductor markers
CLI C 1-3 GE/SW Å MP**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen



Product is similar to illustration