

**Cable glands
VP 21-K54**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

General ordering data

| | |
|------------|--|
| Type | VP 21-K54 |
| Order No. | 0295160000 |
| Version | Cable glands, Blanking plug, Polyamid 6 (PA6 - GF30), RAL 7035, PG 21, IP 54 |
| GTIN (EAN) | 4008190012007 |
| Qty. | 100 pc(s). |

Datenblatt

Cable glands VP 21-K54

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------|-------|------------|-------|
| Length | 12 mm | Net weight | 3.8 g |
|--------|-------|------------|-------|

General information

| | | | |
|-----------------------------------|---------------------------|-----------------------------------|----------|
| Cable gland | PG | Colour code | RAL 7035 |
| DIN | DIN 46320 (for PG thread) | External thread | PG 21 |
| Head diameter | 33 mm | Length of thread | 8 mm |
| Material | Polyamid 6 (PA6 - GF30) | Operating temperature range, max. | 100 °C |
| Operating temperature range, min. | -40 °C | Protection degree with GWDR | IP 65 |
| UL 94 flammability rating | V-2 | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC000032 | UNSPSC | 30-21-18-01 |
| eClass 5.1 | 27-14-91-10 | eClass 6.2 | 27-14-91-10 |
| eClass 7.1 | 27-14-91-10 | | |

Product information

| | |
|---------------------------------|---|
| Descriptive text ordering data | Other versions available on request. The sealing plugs must be tightened "hand-tight" with the screwdriver. |
| Descriptive text technical data | Optional sealing ring |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|