

**Cable glands  
SKMU M40 MS SC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

**General ordering data**

Type	SKMU M40 MS SC
Order No.	<a href="#">0930640005</a>
Version	Cable glands, Locknut, Brass, M 40
GTIN (EAN)	4032248976096
Qty.	10 pc(s).

**Datenblatt**

**Cable glands  
SKMU M40 MS SC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Net weight 35 g

**Width**

Thickness 4.5 mm

**General information**

AF size 1	50 mm	Colour code	Miscellaneous
External thread	M 40	Length of thread	4.5 mm
Material	Brass	Pitch of thread	1.5 mm
Thickness	4.5 mm		

**Classifications**

eClass 6.2	27-14-91-09	eClass 7.1	27-14-92-01
------------	-------------	------------	-------------

**Approvals**

ROHS Conform

**Datenblatt**

**Cable glands  
SKMU M40 MS SC**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

