

## Technische Daten zu 304369

### 24 Bit WAVE / MP3 Recorder

Recording Media: SD memory card (64MB~2GB)

Sample Rate: 44.1 kHz / 48 kHz

Record Format: WAV 16 bit, WAV 24 bit ,

MP3 : 64 kbps, 96 kbps, 128 kbps, 160 kbps, 192 kbps, 224 kbps, 320 kbps

MIC Select: 2 MICS / 4 MICS

Effects: 5 types ( Delay, Chorus, Room, Hall, Pitch, Shift)

Built-in Speaker

Display: 128 x 64 dots OLED

Input: 1/8" Stereo Line Input, 1/8" External MIC

input, Built-in Stereo MIC

Output: 1/8" Headphones.

USB Interface: Mini-B type

Power Requirements: AC adaptor (DC 3V) or AA size (LR6) battery x 2

Dimensions: 67(W) x 29(D) x 107(H)mm

## Electrical requirements:

Parameter

sensitivity

$-58 \pm 3\text{dB}$  ( $0\text{dB}=1\text{V/Pa}$ )

Output impedance

Less than 2.2 k

Directivity

Omni-directional

Power consumption

Less than 500uA

S/N ratio

more than 55dB

Max. input sound level

115 dB SPL

Voltage reduction characteristic

Less than 3dB from 2V to 1.1V

## Frequency Curve

