

SANGEAN

THE WORLD OF LISTENING

Digital Recording Devices / Radio

MODEL		DAR-101	
DISPLAY	LCD / VFD / Dial Scale	LCD	
	View Area (inch)	2.36" x 1.14"	
	Graphic / Character Type	Graphic 128 x 64	
	Back Light	✓	
	Dimmer	✓	
FEATURE	Stereo	Earphones	
	Battery Charger	✓	
MEDIA	Aux - in	✓	
	SD	✓	
	USB	✓	
PERFORMANCE	SD Card Type	SD / MMC / SDHC	
	Playable Media Format	MP3 (16 - 320 Kbps) / WMA (48 - 192 Kbps)	
	Recordable Media	SD / MMC / SDHC	
	Recordable Format	MP3 (64K / 128K / 192Kbps)	
	Timer Recording	✓	
	File Browser	✓	
	File System	FAT 16 / FAT 32	
	Microphone	INTERNAL / EXTERNAL	
	Voice Activated Recording (V.A.R.)	✓	
	Telephone Recording	✓	
	REC Indicator	✓	
CLOCK	Real Time	✓	
OUTPUT DEVICES	Speaker	Size	3 inches
		Impedance	8 ohms
		Magnetically Shield	✓
OUTPUT POWER (TYPICAL)	AC / DC / AC to AC in (Speaker)	1W AC to AC in	
	Batteries (Speaker)	1W	
	Earphones	3mW + 3mW	
POWER SUPPLY	AC to AC in	9V AC / 0.7A	
	Batteries (Main Power)	4 x 1.5V (UM - 3)	
I/O SOCKET	AC to AC in	✓	
	Aux - in	✓	
	MIC IN	✓	
	Earphones	✓	
	Line out	✓	
	SPDIF out	✓	
	Beep out	✓	
	Others	Volume / REC level & balance / REC remote in	
ACCESSORIES	AC to AC Adapter	✓	
	Others	Telephone patch cord	
DIMENSIONS	Width (inch)	7.1	
	Height (inch)	2.0	
	Depth (inch)	5.2	
	Weight (lb. oz)	1 lb. 3.1 oz	
PARTICULAR PERFORMANCE	1	High specification digital voice recorder	
	2	Telephone / music / reminder 3 individual modes in one	