

## Cable glands VG 29-K68

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Screwed joints that comply with the high demands of class of protection IP 68

### General ordering data

Type	VG 29-K68
Order No.	<a href="#">1569030000</a>
Version	cable glands, Polyamide 6, RAL 7035, External thread: PG 29
GTIN (EAN)	4008190142872
Qty.	20 pc(s).

**Datenblatt**

**Cable glands  
VG 29-K68**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	53 mm	Net weight	34.8 g
--------	-------	------------	--------

**General information**

AF size 1	42 mm	Cable gland	PG
Clamping range, max.	25 mm	Clamping range, min.	18 mm
Colour code	RAL 7035	DIN	EN 50262 (for M thread)
External thread	PG 29	Length of thread	11 mm
Material	Polyamide 6	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Seal insert	CR
Torque for cap nut, max.	8 Nm	Torque for cap nut, min.	7 Nm
Torque for connecting adapter, max.	10.5 Nm	Torque for connecting adapter, min.	7.5 Nm
UL 94 flammability rating	V-2		

**Classifications**

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

**Product information**

Descriptive text ordering data	Long-thread version on request, halogen-free without sealing ring
Descriptive text technical data	Version with moulded sealing lip Length L varies depending on the cable diameter used

**Approvals**

Approvals



ROHS	Conform
------	---------