

AUDIO Cosmopolit 7 WEB

**Internetradio, DAB, Audiostreaming
in zeitlosem Aluminium-design**

- Internet Radio ohne Zusatzkosten bei vorhandener DSL Flat Rate.
- Audiostreaming von PC über LAN oder WLAN (802.11 b/g). UPNP client.
- Auswahl aus über 11.000 Radio-stationen über "v-Tuner".
- UKW und DAB Band III Funktion mit jeweils 10 Speicherstationen.
- Inklusive RDS-Radiotext.
- Automatischer und manueller Sendersuchlauf.

**Internet radio, DAB, audiostreaming
in timeless, sophisticated design**

- Internet radio w/o additional costs of an existing DSL flat rate.
- Audio streaming from PC via LAN or WLAN (802.11 b/g). UPNP client.
- More then 11.000 radio stations available over "v-tuner".
- UKW and DAB Band III function each with 10 pre-sets.
- Including RDS radio text.
- Automatically and manual tuning.



Cosmopolit 7 WEB

Verstärkerteil

1,5/1,0 Watt Musik-/Sinusleistung

Tunerteil

Wellenbereiche: UKW, DAB Band III, PLL-Frequenz-Synthesizer-Abstimmung, Programmauswertung PTY, Radio Daten System RDS, RDS -Radiotext, Autom. und manueller Sendersuchlauf, Senderspeicher: 10 FM, 10 DAB, Last Station Memory, Mono/Stereo-Schalter

Stromversorgung

Netzteil: 110-230 V~ via AC adapter, Netzfrequenz: 50 / 60 Hz

Lautsprecher

1x 77 mm Breitband

Display

LC-Display

Anschlüsse

Anschluss für Stereo-Kopfhörer, externes Netzteil, LAN (10/100 Bit), WLAN (802.11b/g), WEP, WPA, WPA2

Allgemein

USB Host Funktion vorbereitet; Q1/2009 Firmware update

Gehäuse (BxHxD, mm)

252 x 127 x 79 mm

Gewicht

1,083 kg

Uhr

Automatische Uhrzeiteinstellung über Internet, FM- oder DAB-Empfang, Wecken mit Musik oder Alarmsignal, Timer einstellbar bis zu 300 Min., 12 / 24 Stunden Umschaltung, Nachwecken in 5-Min-Abständen möglich, 2 Weckzeiten, Einschlafzeit-Automatik bis zu 60 Min. programmierbar

Lieferumfang

Garantie-Hinweis, Bedienungsanleitung, Fernbedienung

Farbe

Aluminium

Amplifier Part

1,5/1,0 Watt music- / nominal power

Tuner Part

Wave bands: FM, DAB Band III, PLL frequency synthesizer tuning, Program Type Identification PTY, Radio Data System RDS, RDS radio text, Automatic and manual station search, Station presets: 10 FM, 10 DAB, Last station memory, Mono/stereo switch

Power Supply

Mains supply: 110-230 V~ via AC adapter, Mains frequency: 50 / 60 Hz

Loudspeaker

1x 77 mm wide range

Display

LC display

Connections

Stereo headphone connection, external power supply, LAN (10/100 Bit), WLAN (802.11b/g), WEP, WPA, WPA2

General

Ready for USB host function; firmware update Q1/2009

Cabinet (WxHxD, mm)

252 x 127 x 79 mm

Net weight

1,083 kg

Clock

Automatic time setting via internet, FM- or DAB reception, Alarm by radio, CD or by buzzer signal, Timer function up to 300 minutes, 12 / 24 hours time mode, 5-minute-interval repeat alarm facility (snooze), 2 alarm times, Sleep function, programmable up to 60 minutes

Included in delivery

Warranty sheet, instruction booklet, remote control

Color

Aluminium