

Accessories
SKMU PG7-K SW**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU PG7-K SW
Order No.	1719100000
Version	Accessories, Locknut, Polyamid 6 (PA6 - GF30), PG 7
GTIN (EAN)	4008190352325
Qty.	50 pc(s).

**Accessories
SKMU PG7-K SW**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 1.37 g

Width

Thickness 5 mm

General information

AF size 1	19 mm	Cable gland	PG
Colour code	RAL 9005	External thread	PG 7
Internal thread	PG 7	Length of thread	5 mm
Material	Polyamid 6 (PA6 - GF30)	O.D.	21.95 mm
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Thickness	5 mm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000940	UNSPSC	30-21-18-01
eClass 5.1	23-11-07-01	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Further versions on request
Descriptive text technical data	approval not required

Approvals

Approvals



ROHS Conform

Datenblatt

Accessories
SKMU PG7-K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

