

**Accessories  
VP 29-EXE SW**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP 29-EXE SW
Order No.	<a href="#">1719300000</a>
Version	Accessories, Blanking plug, Polyamide, RAL 9005, PG 29, IP 66
GTIN (EAN)	4008190352554
Qty.	20 pc(s).

**Accessories  
VP 29-EXE SW**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	19 mm	Net weight	11.65 g
--------	-------	------------	---------

**Approvals**

Approval for cable gland	II 2 GD, Ex d IIC, Ex e II, Ex tD
--------------------------	-----------------------------------

**General information**

AF size 1	40 mm	Cable gland	PG
Colour code	RAL 9005	External thread	PG 29
Length of thread	13.5 mm	Material	Polyamide
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Protection degree with GWDR	IP 68	Torque for cap nut, max.	8 Nm
Torque for cap nut, min.	8 Nm	Torque for connecting adapter, max.	8 Nm
Torque for connecting adapter, min.	8 Nm	UL 94 flammability rating	V-2

**Classifications**

ETIM 3.0	EC000032	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-10	eClass 6.2	27-14-91-12
eClass 7.1	27-14-91-12		

**Product information**

Descriptive text ordering data	Refer to the enclosed installation instructions for the tightening torque.
Descriptive text technical data	Optional sealing ring

**Approvals**

Approvals



ROHS	Conform
------	---------