

**Device markers
THM EL 38 WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



THM EL are adhesive-backed roll-packaged continuous labels in 15 mm, 24 mm, 38 mm and 45 mm widths. Using M-Print® PRO, you can set and adjust the required length to meet your requirements.

THM Plus S, equipped with an additional cutting unit, is optimally suitable for printing.

General ordering data

Type	THM EL 38 WS
Order No.	1105560000
Version	Device markers, Label, 30 x 38 mm, Vinyl film, Colour: White
GTIN (EAN)	4032248880775
Qty.	1 pc(s).

Datenblatt

Device markers THM EL 38 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	30 m	Width	38 mm
Net weight	380 g		

General data

Adhesive	Polyacrylate adhesive	Colour	White
Material	Vinyl film	Material colour according to resistance code	9
Number per roll	1	Number per sheet	1
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Printing method	Thermotransfer	UL 969 flammability rating	No

Classifications

ETIM 3.0	EC001288	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file	str_thm_el_38_mcf.zip
---------------------------------	---------------------------------------