



Werkstoff: Polystyrol, schwarz
Längentoleranz: $\pm 0,15$ mm
Wärmefest bis: 70°C
Zwischenlängen: ab 3000 Stück

* : \diamond = ab Lager, X = ab 1000 Stück, PG = Preisgruppe

Type	D1	D2	L	PG*	*
1005-02	4,5	8	2	027	\diamond
1005-02,5	4,5	8	2,5	027	\diamond
1005-03	4,5	8	3	027	\diamond
1005-04	4,5	8	4	027	\diamond
1005-05	4,5	8	5	016	\diamond
1005-05,5	4,5	8	5,5	031	\diamond
1005-06	4,5	8	6	031	\diamond
1005-07	4,5	8	7	031	\diamond
1005-08	4,5	8	8	031	\diamond
1005-09	4,5	8	9	031	\diamond
1005-10	4,5	8	10	017	\diamond
1005-10,5	4,5	8	10,5	033	\diamond
1005-11	4,5	8	11	033	\diamond
1005-12	4,5	8	12	033	\diamond
1005-13	4,5	8	13	033	\diamond
1005-14	4,5	8	14	033	\diamond
1005-15	4,5	8	15	021	\diamond
1005-16	4,5	8	16	037	\diamond
1005-16,5	4,5	8	16,5	037	\diamond
1005-17	4,5	8	17	037	\diamond
1005-18	4,5	8	18	037	\diamond
1005-19	4,5	8	19	037	\diamond
1005-20	4,5	8	20	027	\diamond
1005-21	4,5	8	21	041	\diamond
1005-22	4,5	8	22	041	\diamond
1005-23	4,5	8	23	041	\diamond
1005-24	4,5	8	24	041	\diamond
1005-25	4,5	8	25	030	\diamond
1005-25,5	4,5	8	25,5	045	\diamond
1005-26	4,5	8	26	045	\diamond
1005-26,5	4,5	8	26,5	045	\diamond
1005-27	4,5	8	27	045	\diamond
1005-28	4,5	8	28	045	\diamond
1005-29	4,5	8	29	045	\diamond
1005-30	4,5	8	30	035	\diamond

Type	D1	D2	L	PG*
1005-31	4,5	8	31	049
1005-32	4,5	8	32	049
1005-33	4,5	8	33	049
1005-34	4,5	8	34	049
1005-35	4,5	8	35	041