

Feed-through terminal block - MXK 4 - 0561002

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Width: 6.2 mm, Color: gray, Mounting type: NS 15



Key commercial data

package_quantity	50
GTIN	4017918002909

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Inflammability class according to UL 94	V0

General

Nominal current I _N	32 A
Nominal voltage U _N	690 V
Open side panel	ja

Dimensions

Width	6.2 mm
Length	28 mm
Height NS 35/7,5	38 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	12

Feed-through terminal block - MXK 4 - 0561002

Technical data

Connection data

Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141123
eCl@ss 4.1	27141123
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897


UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

ATEX / IECEx / GOST / GOST /

Approval details



	
Nominal voltage UN	440 V
Nominal current IN	27 A

Feed-through terminal block - MXK 4 - 0561002

approvals

mm ² /AWG/kcmil	0.2-4
----------------------------	-------

IECEX	
Nominal voltage UN	440 V
Nominal current IN	27 A
mm ² /AWG/kcmil	0.2-4



accessories

Mounting rail

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682



NS 15 AL PERF 2000MM - 1401763



Feed-through terminal block - MXK 4 - 0561002

accessories

NS 15 WH PERF 2000MM - 1204096



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>