


UNIVERSAL ELECTRONICS INDUSTRIES LTD.  
PART LIST FOR WCC-1500ST(230V) (CE)

NO.	CODE NO.	DESCRIPTION
ITEM NO: TC-1500S (S.1)		
1	H.K.P. P-TC,W-W1500ST	TOP COVER (WHITE)
2	H.K.P. M-SC-W2000	SCREW CAP (YELLOW)
3	H.K.P. S-1PM1.7W4	SCREW 1.7 X 4 IP/HS (W)
4	H.K.P. LW-A24R100	LEAD WIRE AWG24 300V RED 100MM
5	H.K.P. LW-A24B80	LEAD WIRE AWG24 300V BLACK 80MM
ITEM NO: CB-1500-ST2 (S.2)		
6	H.K.P. CB-1500E	CIRCUIT BOARD (1500E)
7	H.K.P. M-EL1.2X4.5	EYELET 1.2 X 4.5
8	H.K. D-1N4007	DIODE 1N4007
9	H.K.P. D-K1500E,70	SIDAC K1500E70
10	H.K. CO-C3A	TRIGGER COIL C-3A(3 WIRES)
11	H.K. SRT	SILICON TUBE 2 X 8 MM
12	C.Y. M-FTS-W1500	FLASH TUBE SUPPORTOR
13	H.K. FT-3635S	FLASH TUBE #3635S
14	H.K. C-PFC-0.047/400	CAPACITOR 0.047 MFD/400V
15	H.K. R-1.5KH,FU	FUSIBLE RESISTOR 1.5K OHM 1/2W
16	H.K. R-20M	RESISTOR 20M OHM 1/4W
17	H.K. R-3.3M	RESISTOR 3.3M OHM 1/4W
ITEM NO: W1500-A (S.3)		
18	H.K. C-EC-10/350	ELECTRIC CAPACITOR 10MFD/350V
19A	P.L. P-SB,R-W1500	STROBE BODY (RED)
19B	P.L. P-SB,BL-W1500	STROBE BODY (BLUE)
19C	P.L. P-SB,O-W1500	STROBE BODY (ORANGE)
19D	P.L. P-SB,T-W1500	STROBE BODY (TRANSPARENT)
20	H.K. PP-RR-W1500	RUBBER KING
21	H.K.P. S-RRT3W15	SCREW 3 X 15 RH/ST (W)
ITEM NO: TC-1500S, CB-1500-ST2.		
ITEM NO: W1500-N-1A (S.4)		
22	H.K.P. LB-SL156	SQUARE LABEL WCC1500 220V 50HZ
23	H.K.P. LB-SL126	SQUARE LABEL AC STROBE CE95

Flashes : 60-80 times per minutes  
 Visibility : 2 miles  
 Power Consumption : less than 1W  
 AC Voltage : 220-240V  
 Color : Clear/Red/Blue/Amber  
 Screw Type: E-27



MODEL	WOC-1500		DESCRIPTION	Circuit Diagram 230VAC		
SCALE		MATERIAL		DRAWN BY	S.K.	85.
DESIGN NO.		TREATMENT		CHECKED BY		
PART NO.		QUANTITY		APPROVED BY	S.K.	Apr. 96
CODE NO.		REMARK				DATE
UNIVERSAL ELECTRONICS INDUSTRIES LTD.						