



Specification

Sound Level	≥ 90dB at 12VDC/30cm
Resonant Frequency	2.9 ± 0.5kHz
Input Voltage	6.0 ~ 24 VDC
Tone Nature	Dual (Consecutive/ Disconnected)
Current Consumption	20mA max. at 12VDC
Operating Temperature	-20 ~ 60°C
Operating Humidity	95% RH
Housing material	ABS (Black)
Product Weight	approx. 46.5g

DATE	REVISION	APPROVAL BY	DIMENSION	mm	MODEL	43P29C
			DRAW BY	Oscar Wong	NAME	IP58 Waterproof Buzzer (High dB)
			APPROVAL BY	Rikki So		
			DATE	25-04-13		