



DATA SHEET	52105270
SKINDICHT® SHV-M	valid from : 08.04.2009

The SKINDICHT® SHV-M is a water pressure-tight cable gland for extremely demanding applications.
The special conical seal element is pulled through the entire gland and thus ensures excellent compression strength and strain relief.



Component parts:

Body:	nickel plated brass
Dome nut:	nickel plated brass
Cone seal:	CR/NBR
Pressure cone:	nickel plated brass
Flat washer:	galvanized steel
O-Ring:	NBR

Technical features:

Connecting thread:	M 12x1,5 up to M 32x1,5 in acc. to DIN EN 60 423, table. 1
Protection class:	IP 68 – 10 bar test in acc. to EN 60 529
Temperature range:	- 20° C up to + 80° C

Other Characteristics:

gentle cable clamping
Robust

Norm references:



For more information please see our current catalogue.
Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by: TE-VZ: M.Steinberg	Document: DB52105270EN	page 1 of 1
--------------------------------------	------------------------	-------------