

Speaker Cable With OFC Datasheet



Temperature range min. -20°C
 Temperature range max. 105°C

B/N	603974	603986	604060	603961
Item No.	2X0.75 speaker cable	2X1.5 speaker cable	2X2.5 speaker cable	2X4 speaker cable
Jacker, outer dimension	7.1X0.9 mm	7.1X0.9 mm	7.1X0.9 mm	7.1X0.9 mm
No. of conductors	2X0.75 sqmm	2X1.5 sqmm	2X2.5 sqmm	2X4 sqmm
CCA strand per conductor	66X0.12 mm	132X0.12 mm	221X0.12 mm	353X0.12 mm
color	transparent with red	transparent with red	transparent with red	transparent with red
Packaging	30m	30m	30m	10m