

Product Description

A transparent foil is wrapped around the cable and pasted over the printed field, so that the printing is protected against abrasion, moisture, oils and solvents



Application range

- Very suitable for marking cables and switch cabinets

Benefits

- A transparent foil is wrapped around the cable and pasted over the printed field, so that the printing is protected against abrasion, moisture, oils and solvents

Design

- LCK labels for laser printers
- On DIN-A4 sheets. We recommend the use of original toner. Insert sheet in manual paper feed compartment. Optimum printing results from laser printers are achieved with straight sheet feed-in with no deflection over rollers and little heat build-up

Product features

- White or yellow labelling field
- Printing fields can be printed with laser printer by using the FLEXIMARK® software, or marked with waterproof, permanent MS marker pens

**Technical Data****Caution**

Halogen-free

Colour delivered

White or yellow labelling field

Material

Polyester film

Thickness: 0.025 mm

Temperature range

-40°C to +125°C

Minimum working temperature: +10°C

Article List

Part number	Article designation	Width (mm) x length (m)	Labelling surface (mm)	For outer Ø (mm)	Labels per side	Contents (unit)	PU
LCK labels for laser printers							
83256143	FLEXIMARK Label LCK 32 25-35.5 WH	25 x 35,5	25 x 12,7	4 - 7	64	640	1
83256142	FLEXIMARK Label LCK 32 25-35.5 YE	25 x 35,5	25 x 12,7	4 - 7	64	640	1
83256145	FLEXIMARK Label LCK 35 25-57 WH	25 x 57	25 x 19	6 - 12	40	400	1
83256144	FLEXIMARK Label LCK 35 25-57 YE	25 x 57	25 x 19	6 - 12	40	400	1
83256147	FLEXIMARK Label LCK 40 25-95 WH	25 x 95	25 x 25,4	8 - 22	24	240	1
83256146	FLEXIMARK Label LCK 40 25-95 YE	25 x 95	25 x 25,4	8 - 22	24	240	1
83256149	FLEXIMARK Label LCK 45 25-142.5 WH	25 x 142,5	25 x 25,4	8 - 37	16	160	1

83256148	FLEXIMARK Label LCK 45 25-142.5 YE	25,5 x 142,5	25,5 x 25,4	8 - 37	16	160	1
83256160	FLEXIMARK Label LCK 48 35-95 WH	34 x 95	34 x 25,4	8 - 22	18	180	1
83256161	FLEXIMARK Label LCK 48 35-95 YE	34 x 95	34 x 25,4	8 - 22	18	180	1
83256151	FLEXIMARK Label LCK 60 50-57 WH	50 x 57	50 x 19	6 - 12	20	200	1
83256150	FLEXIMARK Label LCK 60 50-57 YE	50 x 57	50 x 19	6 - 12	20	200	1
83256153	FLEXIMARK Label LCK 65 50-95 WH	50 x 95	50 x 25,4	8 - 22	12	120	1
83256152	FLEXIMARK Label LCK 65 50-95 YE	50 x 95	50 x 25,4	8 - 22	12	120	1
83256155	FLEXIMARK Label LCK 70 50-142.5 WH	50 x 142,5	50 x 25,4	8 - 37	8	80	1
83256154	FLEXIMARK Label LCK 70 50-142.5 YE	50 x 142,5	50 x 25,4	8 - 37	8	80	1

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.

Contents: roll, metre, unit, marker, label