

# Varta Photobatterien: Die auslösende Kraft.

	Typ-Nr	Order-Nr.	Spannung (Volt)	System	Kapazität (mAh)	Maximale Abmessungen ø mm   Höhe (mm)		Gewicht (g)	Verpackung/Blister	Duracell	UCAR	Panasonic	Kodak	Berec	Ray-O-Vac	Sonstige Hersteller
	V 1 PX	4002 101 401	1,35	Mercury	1100	16,4	16,8	12	10 x 1er/100 x 1er	PX1/RM 1 N	EPX 1	MR 50	-	PX 1/RM 1 N	RPX 1/T 1 N	P, TH-MP, TH-KN, M 1 P, H-P
	V 14 PX	4015 101 401	2,7	Mercury	420	16,8	16	10	10 x 1er/100 x 1er	PX 14	EPX 14	H-2 D	-	PX 14	RPX 14	HS-2D KM-2D, TH-2 MC, 2 MR 9
614629 →	V 23 PX	4023 101 401	5,6	Mercury	100	15,2	20	12	10 x 1er/100 x 1er	PX 23	EPX 23	PX 23	KX 23	PX 23	RPX 23	-
614637 →	V 27 PX	4027 101 401	5,6	Mercury	145	12,85	20,5	10,2	10 x 1er/100 x 1er	PX 27	EPX 27	PX 27	KX 27	PX 27	RPX 27	HS-3 C, 4 NR 43
	V 28 PX	4028 101 401	6	Silver	145	13	25,2	11,1	10 x 1er/100 x 1er	PX 28	544	4 SR 44	KS 28	PX 28	RPX 28	4 NZ-13, 4 SR 44, G 13
	V 28 PXL	6231 101 401	6	Lithium	170	13	25,1	8,8	10 x 1er/100 x 1er	PX 28 Lith.	L 544	-	K 28 L	-	-	-
614645 →	V 4034 PX	4034 101 401	6	Alkali-Mangan	100	13	25,2	10,4	10 x 1er/100 x 1er	7 H 34	537	4 LR 44	-	7 H 34	-	4 LR 44
614670 →	V 72 PX	4072 101 401	22,5	Alkali-Mangan	70	26 x 15 x 50		39	10 x 1er/100 x 1er	MN 122	412	-	-	-	215	-
614661 →	V 74 PX	4074 101 401	15	Alkali-Mangan	45	16	35	14	10 x 1er/100 x 1er	MN 154	504	-	KA 74	-	220	-
	V 76 PX	4075 101 401	1,55	Silver	145	11,6	5,4	2,4	10 x 1er/100 x 1er	10 L 14/D 357	EPX 76	SR 44	KS 76	B-SR 44 H	RW 22/42	G 13, GS 13, G 13 F, SR 44
	V 164 PX	4164 101 401	5,6	Mercury	550	17	45	33	10 x 1er/100 x 1er	TR 164 R	EPX 164	HM-4 N	-	-	-	KM-4 N, 4 MR 52
	V 400 PX	4400 101 401	1,35	Mercury	80	11,6	3,6	1,1	10 x 1er/100 x 1er	PX 400	EPX 400	H-B	KX 400	PX/RM 400	T 400 N	B, HS-B, M-1 B
614505 →	V 625 PX	4625 101 401	1,35	Mercury	450	16	6,2	4,6	10 x 1er/100 x 1er	PX 625	EPX 625	MR 9	KX 625	PX 625	RPX 625	D, M-D, HS-D, M-1 D, TH-MC, H-D
614750 →	V 625 U	4626 101 401	1,5	Alkali-Mangan	190	16	6,2	3,3	10 x 1er/100 x 1er	-	EPX 625 G	-	KA 625	-	R 625	-
	V 640 PX	4640 101 401	1,35	Mercury	550	16,4	11,4	7,9	10 x 1er/100 x 1er	PX 640	EPX 640	M 52	KX 640	PX/RM 640	-	H, M-N, HS-N, HM-N, M-1 N
614513 →	V 675 PX	4677 101 401	1,35	Mercury	210	11,6	5,4	2,7	10 x 1er/100 x 1er	PX 675	EPX 675	MR 44	KX 675	PX 675	RPX 675	C, HS-C, M-C, M-1 C, TH-KC
	V 825 PX	4825 101 401	1,5	Alkali-Mangan	350	23	6,1	7,2	10 x 1er/100 x 1er	PX 825	EPX 825	PX 825	KA 825	PX 825	TPX 825	LR 53
	V 1500 PX	4206 101 404	1,5	Alkali-Mangan	-	14,5	50,5	23	20 x 4er/100 x 4er	MN 1500	E 91	LR 6	KA A-P	LR 6	815	LR 6, AM 3
	V 2400 PX	4203 101 404	1,5	Alkali-Mangan	-	10,5	44,5	11	10 x 4er/ 50 x 4er	MN 2400	E 92	LR 03	K 3 A-P	LR 03	824	LR 03, AM 4
	CR 1/3 N	6131 101 401	3	Lithium	170	11,6	10,8	3	10 x 1er/100 x 1er	DL 1/3 N	2 L 76	-	K 58 L	-	-	-
626490 →	2 CR 5	6203 101 401	6	Lithium	1500	34 x 17 x 45		42	10 x 1er/100 x 1er	DL 245	2 CR 5	-	KL 2 CR	-	-	-
615226 →	CR-P 2	6204 101 401	6	Lithium	1300	34 x 19,5 x 36		38	10 x 1er/100 x 1er	DL 223 A	EL 223 A	CR-P 2p	K 223 L	-	-	-
615290 →	CR 123 A	6205 101 401	3	Lithium	1300	16,9	34	16	10 x 1er/100 x 1er	DL 123 A	EL 123 A	CR 123	K 123 L	-	-	-
	4001	4001 101 401	1,5	Alkali-Mangan	-	12	30,2	10	1/10/100	MN 9100	E 90	LR 1	K N	244	810	-
	4014	4014 101 402	1,5	Alkali-Mangan	-	26,2	50	64,5	2/20/200	MN 1400	E 93	LR 14	KC	241	814	-
	4018	4018 101 401	6	Alkali-Mangan	-	48,2 x 9,0 x 35,5		34	1/10/50	7 K 67	539	-	KJ	-	-	-
	4020	4020 101 402	1,5	Alkali-Mangan	-	34,2	61,5	127	2/20/100	MN 1300	E 95	LR 20	KD	240	813	-
	4022	4022 101 401	9	Alkali-Mangan	-	26,5 x 17,5 x 48,5		46	1/10/200	MN 1604	522	6 LF 22	K 9 V	249	-	-
	V 12	5912 101 111	12	Pb	2000	182 x 61 x 22		620	1/5/20							
	V 20	5920 101 111	12	NC	1600	154 x 72 x 48		570	1/5/20							
	V 22	5922 101 111	6	NC	1600	115 x 50 x 25		290	1/5/40							
	V 30	5930 101 111	6	NC	1000	90 x 47 x 23		152	1/5/40							
	V 61	5961 101 111	9,6	NC	1400	112 x 68 x 28,5		295	1/5/40							
	V 66	5966 101 111	6	NC	1900	90 x 47 x 48		296	1/5/40							
	V 70	5970 101 111	9,6	NC	1700	112 x 64 x 47		470	1/5/20							
	V 80	5980 101 111	7,2	NC	1000	93 x 53 x 19		180	1/5/40							



Varta Batterie AG · Am Leineufer 51 · 3000 Hannover 21 · West Germany · Telefon 05 11/79 03-0  
Telex 9 22 124 oder 921175-66 · Telefax 05 11/7 903 622