

MODEL: CW-324

Volume: 24 Litres

Voltage: DC12V Only; AC110V/DC12V; AC230V/DC12V

Power consumption: AC MAX POWER: Cool Mode 70W±20%
Hot Mode 65W±20%

DC MAX POWER: 60W

Cooling capacity: 20°C--24°C below ambient temperature
+5°C(set-point thermostat).

Heating capacity: +65°C by set-point thermostat

HOT-OFF-COLD: Brushless motor for long life operation.

INSULATION: Solid CFC-free polyurethane foam

SYSTEM: ● Select switch with LED indication for the functions.

- Non-wearing thermoelectric (Peltier System).
- Handle recess when not in use.
- Equipped with 2 pcs long life brushless motor (30,000 hours), one for heat dissipation to outside the other for inside cooling/warming ventilation.
- With light inside, foods in the fridge can be seen in very dark environment.
- Cap.24 litres/Even 4x2litre bottle or even 30x355ml cans.