

Gitarrenkabel **ROAD LINE**[®] CGK ROAD 75
 Guitar cable **ROAD LINE**[®] CGK ROAD 75



ROAD-TAUGLICH: Flexible LowNoise / Lowest Capacity - Meterware, sehr widerstandsfähiger Geflechschirm - Aufbau, dämpfungsarm durch 0,75 mm² Leiterquerschnitt Conductive Plastic.

ROADWORTHY: flexible Low Noise / Lowest Capacity bulk cables, extremely resistant braided shield design, low attenuation due to 0.75 mm² conductor cross-section, conductive plastic.

Leiter/Conductor		Elektrische Werte/Electrical data		
Leiterquerschnitt/Conductor area	0.75 mm ²	Leiterwiderstand/Conductor resistance	24.4 Ohm/km	
Leiteraufbau/Composition of conductor	42 x 0.15 mm CU blank/bare copper	Kapazität (Leiter/Leiter)/Capacity (Cond./Cond.)	76 pF/m	
Mantel/Jacket	Farbe/Color	Durchmesser/Diameter	Gewicht/Weight	Bestell-Nr./Part No.
PVC matt/PVC mat	■	7.2 +/- 0.2	60 g/m	CGK ROAD 75