



ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.1mm 00.= ±0.2mm

<p><b>HEAVY POWER CO., LTD.</b>  <i>A Specialist Manufacturer</i></p> <p>No. 7, Lane 106, Wukung 3rd. Road,  Wuku Industrial Park, Taipei Hsien,  Taiwan 248</p> <p>Tel : 886-2-22983178  Fax : 886-2-22983183</p>	<p><b>Scale :</b></p>	<p><b>Date :</b> 03 / 29 / 2005</p>	<p><b>TITLE :</b></p> <p>TERMINAL BLOCK</p> <p>PART NO. PA11-3</p>	
	<p><b>Housing Material :</b> Polyamide 66 , UL 94V-2  <b>Terminal Insert :</b> Steel , zinc plated  <b>Screws :</b> M3x7 , zinc plated  <b>Working Temperature :</b> -40° C to T110° C (VDE)  105° C (UL)  <b>Voltage :</b> 450V (VDE) ; 300V (UL)  <b>Current :</b> 12A  <b>Push-in Side :</b> 0.5-1.5mm<sup>2</sup> Solid , 20-16 Solid AWG  <b>Screw-in Side :</b> 2.5mm<sup>2</sup> Rigid/Flexible , 18-14 Solid AWG</p>			
<p><b>DWG NO.</b></p> <p>PA11-3</p>	<p><b>International Approvals:</b></p> <p>UL : E152546  CE, CQC, VDE, FIMKO</p>		<p><b>PREPARED</b></p> <p>Lily</p>	<p><b>REV.</b></p> <p>2.0</p>