

變化表：

84 2095 Oil pressure analog gauge +/- 3%

Bar 0 1 5 7

Ω 0 128 384 90

84 2109 Oil temperature analog gauge

25 °C 2000 Ω

40 °C 1056 Ω

50 °C 709 Ω

60 °C 493 Ω

70 °C 349 Ω

80 °C 252 Ω

90 °C 185 Ω

100 °C 137.7 Ω

110 °C 104.2 Ω

120 °C 80.1 Ω

130 °C 62.4 Ω

140 °C 49.2 Ω

150 °C 39.3 Ω

MAX +5%

MIN -5%