



R1: 12.4K OHM
R2: 10K OHM
R3: 15K OHM
R4: 10K OHM
R5: 2.5M OHM
R6: 20K OHM
R7: 10K OHM
R8: 1.5K OHM
R9: 1.5K OHM
R10: 680 OHM
R11: 680 OHM
C1 C2: 0.1uF

C3 C4: 10uF/16V
C5: 2.2uF/16V
C6: 100uF/25V
D1 D2: IN4001 DIODE
D3: DC11V-REGULATOR DIODE
LED1: 2.5x5mm RED LED
LED2: 2.5x5mm GREEN LED
IC1: LM339
IC2: 78L05
Q: 468 TRIODE
J: DC12V/10AMP ELECTRIC RELAY