



R1: 12.4K OHM  
R2: 10K OHM  
R3: 15K OHM  
R4: 10K OHM  
R5: 2.5M OHM  
R6: 20K OHM  
R7: 10K OHM  
R8: 1.5K OHM  
R9: 1.5K OHM  
R10: 680 OHM  
R11: 680 OHM  
C1 C2: 0.1uF

C3 C4: 10uF/16V  
C5: 2.2uF/16V  
C6: 100uF/25V  
D1 D2: IN4001 DIODE  
D3: DC11V-REGULATOR DIODE  
LED1: 2.5x5mm RED LED  
LED2: 2.5x5mm GREEN LED  
IC1: LM339  
IC2: 78L05  
Q: 468 TRIODE  
J: DC12V/10AMP ELECTRIC RELAY