

Ref K815 Toggle Switch

Dear Mirja

Further to your two requests for information relating to the K815 Switch I confirm as follows.

Description	On/On Toggle Switch
	Electrical connections - three copper male 6.3mm terminals
Operating Voltage	12 volt DC
Amps/Load	@ 12v DC 20A (resistive load)
Contact Resistance	20m Ω Max
Insulation Resistance	DC500v 1000M Ω Minimum
Dielectric Strength	AC1500V ~ 1Minute
Operating Temperature	-25°C ~ 45°C
Operating Life	20000 Operations

HP - No. 28.900

Conrad Art. - No. 852943