

SAT-Koaxialkabel

Technische Daten:

Through loss at 100m length:

47MHz 4,8dB
200MHz 9,0dB
500MHz 14,9dB
1000MHz 23,0dB
1750MHz 29,5dB
2050MHz 33,0dB
2400MHz 36,0dB

Return loss:

>25dB/862MHz
>20dB/2050MHz

Impedance:

75 Ohm

Inner conductor:

StCu-wire 1,0mm diameter

Screening:

Al-Foil and Al braiding

Dielectric:

4,8 mm, physically foamed

outer sheath:

PVC 6,8mm

Braiding:

64x0,12mm

Printing on cable / Degressive metering:

Depending on packaging
Example SKB 88-04 Starting with "250m.....1m"

Packaging:

100m paper spool
250m Optibox
500m Wooden drum
10/20/40m sets with F connectors and rubber sleeves.

Weight:

44kg/1000m.

Shielding:

>85dB 30...2150MHz

Datum: 31. Mai 2007 2 (2)

SAT-Koaxialkabel

Schirmungsmaß:

