



REV.	DESCRIPTION	ENG.	APPROVAL



NOTE: HDB15M HDB15F

1. CABLE:28AWG,UL2919,AL+B,3 COAX+4C BLACK DENTATE OD=8.0mm PVC JACKET.(AM BRAID)
2. LENGTH:5000mm
3. CONNECTOR:HDB15M\*1(9 PIN OUT),HDB15F\*1,NICKEL PLATED,BLACK INSULATOR.
4. SCREW :HD37.7 SCREW\*4PCS.

5. CONTACTS:



6. MOLD:SQUARE MOLDING

7. OPEN/SHORT TEST: 100% TEST.  
INSULATIONS: 2M.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF INTRACOM Asia Co.,Ltd. AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF INTRACOM Asia Co.,Ltd.

UNLESS OTHERWISE SPECIFIED:DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE±1°

TOLERANCE( INCH )	TOLERANCE( MM )
x ±0.02"	x ±0.5mm
x.x ±0.01"	x.x ±0.20mm
x.xx ±0.008"	x.xx ±0.15mm
x.xxx ±0.005"	x.xxx ±0.10mm

TITLE:		APPD	Date		
		Check	2008.03.08		
CUSTOMER:		Drawer			
CUSTOMER P/N:		Unit	mm	Projection	☞
ICT P/N:		Scale	1:1	Size:	A4
DWG.NO:		Sheet	1 of	REV.	A