

BN	Product	Model	Lux value	Outer ø	Resolution of image sensor
101048	1M Flexible type cable with dia.5.5mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6100C	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101049	2M Flexible type cable with dia.5.5mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6200C	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101050	3M Flexible type cable with dia.5.5mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6300C	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101051	5M Flexible type cable with dia.5.5mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6500C	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101053	10M Flexible type cable with dia.5.5mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-61000C	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101054	1M Flexible type cable with dia.4.0mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-4100C	700 Lux at 15mm	4.0mm	320(H)*240(V) (76800 Pixels)
101056	2M Flexible type cable with dia.4.0mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-4200C	700 Lux at 15mm	4.0mm	320(H)*240(V) (76800 Pixels)
101057	3M Flexible type cable with dia.4.0mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-4300C	700 Lux at 15mm	4.0mm	320(H)*240(V) (76800 Pixels)
101058	5M Flexible type cable with dia.4.0mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-4500C	700 Lux at 15mm	4.0mm	320(H)*240(V) (76800 Pixels)
101059	10M Flexible type cable with dia.4.0mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-41000C	700 Lux at 15mm	4.0mm	320(H)*240(V) (76800 Pixels)
101061	3M Fiber cable with simple spool + dia.28mm camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-28300C	7800 Lux at 20mm	28mm	640(H)*480(V) (307200 Pixels)
101063	10M Fiber cable with spool + holder + dia.28mm camera for VOLT CRAFT BS-1000T Scope	MIGS-281000C	7800 Lux at 20mm	28mm	640(H)*480(V) (307200 Pixels)
101064	25M Fiber cable with spool + holder + dia.28mm camera for VOLT CRAFT BS-1000T Scope	MIGS-282500C	7800 Lux at 20mm	28mm	640(H)*480(V) (307200 Pixels)
101065	1M Semirigid (Ghose neck) cable with dia 5.5mm Camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6100SRC	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101066	2M Semirigid (Ghose neck) cable with dia 5.5mm Camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6200SRC	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)
101067	3M Semirigid (Ghose neck) cable with dia 5.5mm Camera for VOLT CRAFT BS-500 & BS-1000 Scope	MIGS-6300SRC	1000 Lux at 20mm	5.5mm	320(H)*240(V) (76800 Pixels)