

**HDC enclosures
HDC 24B TSBU 1M40G**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 24B TSBU 1M40G
Order No.	1902480000
Version	HDC enclosures, Size: 8, Protection degree: IP 65, Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 40
GTIN (EAN)	4032248592944
Qty.	1 pc(s).

HDC enclosures HDC 24B TSBU 1M40G

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	120 mm	Width	59 mm
Height	61 mm	Net weight	293 g

Dimensions

Total length housing	120 mm	Width housing C	43 mm
Height of housing B	61 mm	Cable entry	w. threading

General data

Housing main material	diecast aluminium
-----------------------	-------------------

Version

Internal thread	M 40	Design of housing	Cable entry from side, Plug housing
Size	8	Design	Standard
Top part/bottom part/lid	upper part	Design of locking system	Side-locking clamp on lower side
Cable entry	w. threading	Size of cable entries	M 40
Number of cable entry on top	0	Number of cable entry sideways	1

Classifications

ETIM 3.0	EC000437	UNSPSC	30-21-18-01
eClass 5.1	27-14-34-19	eClass 6.2	27-26-12-03
eClass 7.1	27-44-02-02		

Approvals

Approvals



ROHS	Conform
------	---------

Datenblatt

**HDC enclosures
HDC 24B TSBU 1M40G**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

