

Z-series, Accessories
ZTA ZT2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Weidmüller offers users of modular terminals of the Z-Series a comprehensive range of accessories that render possible appropriate solutions for all - even non-standard - tasks.

The accessories must comply with the same quality standards as the modular terminals themselves.

General ordering data

Type	ZTA ZT2.5
Order No.	1827080000
Version	Test adapter, Rated control voltage:
GTIN (EAN)	4032248411276
Qty.	25 pc(s).

**Z-series, Accessories
ZTA ZT2.5**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten
Dimensions and weights

Length	20 mm	Width	5.1 mm
Height of lowest version	50.5 mm	Net weight	5.68 g

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Installation advice	Direct mounting	Version	For the terminals
---------------------	-----------------	---------	-------------------

Clampable wires (rated connection)

Type of connection	Plug-in connection	Stripping length	10 mm
Clamping range, rated connection, min.	0.5 mm ²	Clamping range, rated connection, max.	1 mm ²
Tightening torque, min.	0.3 Nm	Tightening torque, max.	0.3 Nm
Wire connection cross section, solid core, max. rated connection	0.5 mm	Wire connection cross section, solid core max. rated connection	1 mm ²
Wire connection cross section, finely stranded, max.	1 mm ²	Wire connection cross-section, finely stranded, min.	0.5 mm

Disconnect terminals

Tightening torque, max.	0.3 Nm	Tightening torque, min.	0.3 Nm
-------------------------	--------	-------------------------	--------

Rated data

Rated cross-section	1 mm ²	Rated voltage	250 V
Rated current	17.5 A		

Material data

Material	Wemid	Colour	Black
UL 94 flammability rating	V-0		

System specifications

Product family	Z-series, Accessories	Type of connection	Plug-in connection
----------------	-----------------------	--------------------	--------------------

Classifications

ETIM 3.0	EC002255	UNSPSC	30-21-18-01
eClass 6.2	27-14-92-14	eClass 7.1	27-14-92-14

Approvals

Approvals



ROHS Conform

Datenblatt

Z-series, Accessories ZTA ZT2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technische Daten

Downloads

STEP	1827080000_35021_ZTA_Z2.5_STP.stp
3D Modell	
