



MATERIAL SAFETY DATA SHEET

I. PRODUCT IDENTIFICATION

MANUFACTURER CETEOR ZI – Rue de la Baronnerie 3 B-4920 HARZE, BELGIUM	CHEMICAL/TRADE NAME Ceteor Cyclone battery Ref. 862520	Valve Regulated Lead-Acid Battery (VRLA) Absorbed Electrolyte Battery
FOR INFORMATION Primary: MACTEC Engineering and Consulting, Inc. Attention: Juliann Cothran (770) 421-3485 Secondary: Environmental, Safety & Health Attention: Eric Murray (800) 523-4622 Fred Ganster (610) 921-4052	CHEMICAL FAMILY/ CLASSIFICATION DATE ISSUED:	Electric storage Battery February 1, 2008 1 of 5
FOR EMERGENCY CHEMTREC (800) 424-9300 24-hour Emergency Response Contact Ask for Environmental Coordinator	CHEMTREC INTERNATIONAL (703) 527-3887 – Collect	

II. HAZARDOUS INGREDIENTS/IDENTITY INFORMATION

	CAS Number	% by Wt.	Approximate Air Exposure Limits (µg/m ³)		
Components			OSHA	ACGIH	NIOSH
Inorganic compounds of: Lead	7439-92-1	75-77	50	50	50
Electrolyte (no fluid/completely absorbed) sulfuric acid/water/solution	7664-93-9	14-16	1000	200	1000
Case Material: Polypropylene	9003-07-0	5-6	N/A	N/A	N/A

NOTE: Inorganic lead and electrolyte (water and sulfuric acid solution) are the primary components of Ceteor Batteries. Other ingredients may be present dependent upon battery type. Polypropylene is the principal case material of batteries.

III. PHYSICAL DATA

Boiling Point	203° F-240° F (for S.G. range)	Specific Gravity (H ₂ O=1)	1.230 to 1.350
Melting Point	Not Applicable	Vapor Pressure (mm Hg) 77° F	17 to 11 (for S.G. range)
Evaporation Rate (Butyl acetate=1)	Less Than 1	Vapor Density (AIR=1)	Greater than 1
Appearance and Odor	A clear liquid with a sharp, penetrating, pungent odor. A battery is a manufactured article; no apparent odor	% Volatiles by Weight	Not Applicable

IV. FIRE AND EXPLOSION HAZARD DATA

Flash Point:	Not Applicable
Flammable Limits:	LEL = 4.1% (Hydrogen Gas in air) ; UEL = 74.2%
Extinguishing media:	CO ₂ ; foam; dry chemical
Special Fire Fighting Procedures:	Use positive pressure, self-contained breathing apparatus. Beware of acid splatter during water application and wear acid-resistant clothing, gloves, face and eye protection. If batteries are on charge, shut off power to the charging equipment, but, note that strings of series connected batteries may still pose risk of electric shock even when charging equipment is shut down.

IV. FIRE AND EXPLOSION HAZARD DATA (CONTINUED)

Unusual Fire and Explosion Hazards:

In operation, batteries generate and release flammable hydrogen gas. They must always be assumed to contain this gas which, if ignited by burning cigarette, naked flame or spark, may cause battery explosion with dispersion of casing fragments and corrosive liquid electrolyte. Carefully follow manufacturer's instructions for installation and service. Keep away all sources of gas ignition and do not allow metallic articles to simultaneously contact the negative and positive terminals of a battery.

V. REACTIVITY DATA

Stability: Stable
Unstable

Conditions to Avoid: Prolonged overcharge at high current; sources of ignition.

Incompatibility: (materials to avoid)

Electrolyte: Contact with combustibles and organic materials may cause fire and explosion. Also reacts violently with strong reducing agents, metals, sulfur trioxide gas, strong oxidizers, and water. Contact with metals may produce toxic sulfur dioxide fumes and may release flammable hydrogen gas.

Lead compounds: Avoid contact with strong acids, bases, halides, halogenates, potassium nitrate, permanganate, peroxides, nascent hydrogen, and reducing agents.

Hazardous Decomposition Products:

Electrolyte: Sulfur trioxide, carbon monoxide, sulfuric acid mist, sulfur dioxide, hydrogen sulfide.

Lead compounds: Temperatures above the melting point are likely to produce toxic metal fume, vapor, or dust; contact with strong acid or base or presence of nascent hydrogen may generate highly toxic arsine gas.

VI. HEALTH HAZARD DATA

Routes of Entry:

Electrolyte: Harmful by all routes of entry.

Lead compounds: Hazardous exposure can occur only when product is heated above the melting point, oxidized or otherwise processed or damaged to create dust, vapor, or fume.

Inhalation:

Electrolyte: Breathing of sulfuric acid vapors or mists may cause severe respiratory irritation.

Lead compounds: Inhalation of lead dust or fumes may cause irritation of upper respiratory tract and lungs.

Ingestion:

Electrolyte: May cause severe irritation of mouth, throat, esophagus, and stomach.

Lead compounds: Acute ingestion may cause abdominal pain, nausea, vomiting, diarrhea, and severe cramping. This may lead rapidly to systemic toxicity.

Skin Contact:

Electrolyte: Severe irritation, burns, and ulceration.

Lead compounds: Not absorbed through the skin.

Eye Contact:

Electrolyte: Severe irritation, burns, cornea damage, blindness.

Lead compounds: May cause eye irritation.

Effects of Overexposure - Acute:

Electrolyte: Severe skin irritation, damage to cornea may cause blindness, upper respiratory irritation.

Lead compounds: Symptoms of toxicity include headache, fatigue, abdominal pain, loss of appetite, muscular aches and weakness, sleep disturbances, and irritability.

Effects of Overexposure - Chronic:

Electrolyte: Possible erosion of tooth enamel; inflammation of nose, throat, and bronchial tubes.

Lead compounds: Anemia; neuropathy, particularly of the motor nerves, with wrist drop; kidney damage; reproductive changes in both males and females.

VI. HEALTH HAZARD DATA (CONTINUED)

Carcinogenicity:

Electrolyte: The National Toxicology Program (NTP) and the International Agency for Research on Cancer (IARC) have classified "strong inorganic acid mist containing sulfuric acid" as a substance that is carcinogenic to humans. This classification does not apply to sulfuric acid solutions in static liquid state or to electrolyte in batteries. Batteries subjected to abusive charging at excessively high currents for prolonged periods of time without vent caps in place may create a surrounding atmosphere of the offensive strong inorganic acid mist containing sulfuric acid.

Lead compounds: Listed as a 2B carcinogen, likely in animals at extreme doses. Proof of carcinogenicity in humans is lacking at present.

Arsenic: Listed by National Toxicology Program (NTP), International Agency for Research on Cancer (IARC), OSHA and NIOSH as a carcinogen only after prolonged exposure at high levels.

Medical Conditions Generally Aggravated by Exposure:

Overexposure to sulfuric acid mist may cause lung damage and aggravate pulmonary conditions. Contact of electrolyte (water and sulfuric acid solution) with skin may aggravate skin diseases such as eczema and contact dermatitis. Contact of electrolyte (water and sulfuric acid solution) with eyes may damage cornea and/or cause blindness. Lead and its compounds can aggravate some forms of kidney, liver, and neurologic diseases.

Emergency and First Aid Procedures:

Inhalation:

Electrolyte: Remove to fresh air immediately. If breathing is difficult, give oxygen.

Lead compounds: Remove from exposure, gargle, wash nose and lips; consult physician.

Ingestion:

Electrolyte: Give large quantities of water; **do not** induce vomiting; consult physician.

Lead compounds: Consult physician immediately.

Skin:

Electrolyte: Flush with large amounts of water for at least 15 minutes; remove contaminated clothing completely, including shoes.

Lead compounds: Wash immediately with soap and water.

Eyes: Electrolyte and Lead compounds: Flush immediately with large amounts of water for at least 15 minutes; consult physician immediately.

VII. PRECAUTIONS FOR SAFE HANDLING AND USE

Handling and Storage:

Store batteries under roof in cool, dry, well-ventilated areas that are separated from incompatible materials and from activities which may create flames, sparks, or heat. Keep away from metallic objects that could bridge the terminals on a battery and create a dangerous short-circuit. Single batteries pose no risk of electric shock but there may be increasing risk of electric shock from strings of connected batteries exceeding three 12-volt units.

Charging:

There is a possible risk of electric shock from charging equipment and from strings of series connected batteries, whether or not being charged. Shut-off power to chargers whenever not in use and before detachment of any circuit connections. Batteries being charged will generate and release flammable hydrogen gas. Charging space should be ventilated. Keep battery vent caps in position. Prohibit smoking and avoid creation of flames and sparks nearby. Wear face and eye protection when near batteries being charged.

Spill or Leak Procedures:

There is no flow of electrolyte from an Absorbed Electrolyte Battery even if the casing is broken or punctured.

Waste Disposal Methods:

Spent batteries: Send to secondary lead smelter for recycling.

Precautionary Labeling:

POISON - CAUSES SEVERE BURNS

DANGER - EXPLOSIVE GASES

CORROSIVE - CONTAINS SULFURIC ACID

KEEP AWAY FROM CHILDREN

VIII. CONTROL MEASURES

Engineering Controls and Work Practices:

Store and handle in well-ventilated area. If mechanical ventilation is used, components must be acid-resistant. Handle batteries cautiously. Make certain vent caps are on securely. If battery case is damaged, avoid bodily contact with internal components. Wear protective clothing, eye and face protection, when charging or handling batteries.

Respiratory Protection:

None required under normal conditions. When concentrations of sulfuric acid mist are known to exceed PEL, use NIOSH or MSHA-approved respiratory protection.

Protective gloves:

None required under normal conditions. If battery case is damaged, rubber or plastic acid-resistant gloves with elbow-length gauntlet.

Eye Protection:

None required under normal conditions. If battery case is damaged, chemical goggles or face shield.

Emergency Flushing:

In areas where water and sulfuric acid solutions are handled in concentrations greater than 1%, emergency eyewash stations and showers should be provided, with unlimited water supply.

IX. OTHER REGULATORY INFORMATION

NFPA Hazard Rating for sulfuric acid:

Flammability (Red) = 0

Health (Blue) = 3

Reactivity (Yellow) = 2

Sulfuric acid is water-reactive if concentrated.

TRANSPORTATION:

Ceteor absorbed electrolyte batteries meet test specifications for "non-spillable electric storage batteries", as required by D.O.T., 49 CFR 173.159(d), and IMO/IMDG, and ICAO/IATA packing instruction 806 and note A67; therefore, are non-regulated when protected against short circuits, kept upright, and securely packaged.

The battery and the outer packaging must be plainly and durably marked "NONSPILLABLE" or "NONSPILLABLE BATTERY".

RCRA: Spent lead-acid batteries are not regulated as hazardous waste when recycled.

CERCLA (Superfund) and EPCRA:

(a) Reportable Quantity (RQ) for spilled 100% sulfuric acid under CERCLA (Superfund) and EPCRA (Emergency Planning and Community Right to Know Act) is **1,000 lbs.** State and local reportable quantities for spilled sulfuric acid may vary.

(b) Sulfuric acid is a listed "Extremely Hazardous Substance" under EPCRA, with a Threshold Planning Quantity (TPQ) of **1,000 lbs.**

(c) EPCRA Section 302 notification is required if **1,000 lbs** or more of sulfuric acid is present at one site. An average automotive/commercial battery contains approximately 5 lbs of sulfuric acid. Contact your Ceteor representative for additional information.

(d) EPCRA Section 312 Tier Two reporting is required for non-automotive batteries if sulfuric acid is present in quantities of **500 lbs** or more and/or if lead is present in quantities of 10,000 lbs or more.

(e) **Supplier Notification:** This product contains toxic chemicals that may be reportable under EPCRA Section 313 Toxic Chemical Release Inventory (Form R) requirements. For a manufacturing facility under SIC codes 20 through 39, the following information is provided to enable you to complete the required reports:

<u>Toxic Chemical</u>	<u>CAS Number</u>	<u>Approximate % by Weight</u>
Lead	7439-92-1	75-77
Sulfuric Acid/Water Solution	7664-93-9	14-16

If you distribute this product to other manufacturers in SIC Codes 20 through 39, this information must be provided with the first shipment of each calendar year.

Note: The Section 313 supplier notification requirement does not apply to batteries that are "consumer products".

IX. OTHER REGULATORY INFORMATION (CONTINUED)

TSCA:

Ingredients in Ceteor's Cyclone batteries are listed in the TSCA Registry as follows:

	<u>CAS NO.</u>	<u>TSCA Status</u>
Electrolyte		
Sulfuric acid (H ₂ SO ₄)	7664-93-9	Listed
Inorganic Lead Compound		
Lead (Pb)	7439-92-1	Listed
Lead Oxide (PbO)	1317-36-8	Listed
Lead Sulfate (PbSO ₄)	7446-14-2	Listed

CANADIAN REGULATIONS:

All chemical substances in this product are listed on the CEPA DSL/NDSL or are exempt from list requirements.

CALIFORNIA PROPOSITION 65:

"WARNING: This product contains lead, a chemical known to the State of California to cause cancer, or birth defects or other reproductive harm."

PREPARED BY: CETEOR
ZI – RUE DE LA BARONNERIE 3
B-4920 HARZE
BELGIUM

VENDEE AND THIRD PERSONS ASSUME THE RISK OF INJURY PROXIMATELY CAUSED BY THE MATERIAL IF REASONABLE SAFETY PROCEDURES ARE NOT FOLLOWED AS PROVIDED FOR IN THE DATA SHEET, AND VENDOR SHALL NOT BE LIABLE FOR INJURY TO VENDEE OR THIRD PERSONS PROXIMATELY CAUSED BY ABNORMAL USE OF THE MATERIAL EVEN IF REASONABLE PROCEDURES ARE FOLLOWED.

ALL PERSONS USING THIS PRODUCT, ALL PERSONS WORKING IN AN AREA WHERE THIS PRODUCT IS USED, AND ALL PERSONS HANDLING THIS PRODUCT SHOULD BE FAMILIAR WITH THE CONTENTS OF THIS DATA SHEET. THIS INFORMATION SHOULD BE EFFECTIVELY COMMUNICATED TO EMPLOYEES AND OTHERS WHO MIGHT COME IN CONTACT WITH THE PRODUCT.

WHILE THE INFORMATION ACCUMULATED AND SET FORTH HEREIN IS BELIEVED TO BE ACCURATE AS OF THE DATE HEREOF, CETEOR MAKES NO WARRANTY WITH RESPECT THERETO AND DISCLAIMS ALL LIABILITY FROM RELIANCE THEREON. RECIPIENTS ARE ADVISED TO CONFIRM IN ADVANCE OF NEED THAT THE INFORMATION IS CURRENT, APPLICABLE, AND SUITABLE FOR THEIR PARTICULAR CIRCUMSTANCES.

ANY PHOTOCOPY MUST BE OF THIS ENTIRE DOCUMENT