



<b>DATA SHEET</b>	0151005
<b>DIN extension cable KE 3 L 2x1,5 oval</b>	valid from : 01.12.2008

## Application

The extension cable KE 3 L 2 x 1,5 mm<sup>2</sup> is a glass fibre insulated cable which transmits the thermoelectric voltage of Fe/CuNi thermocouples. It is for fixed installation in dry rooms and may only be installed outdoors with UV- and humidity protection and in observation of the max. permitted temperature range.

## Design

Conductor	1,5 mm <sup>2</sup> (48 x 0,20 mm)
Conductor material	LX alloying, accuracy class 2 according DIN 43722 Positive conductor: Fe (iron) Negative conductor: CuNi (cupronickel)
Core insulation	Glass fibre covering
Core identification	Positive conductor: red marked Negative conductor: blue marked
Core layering	Cores parallel next to each other
Outer sheath	Glass fibre braiding with interweaved blue identification thread

## Electrical properties

Limiting deviation class 2      ± 140 µV (± 2,5 °C) / m measuring point temperature +500 °C

## Mechanical and thermal properties

Temperature range	occasional flexing:      -25 °C up to +200 °C
Minimum bending radius	occasional flexing:      12 x cable diameter
Flammability	flame retardant in acc. to IEC 60332-1-2 resp. VDE 0482-332-1-2

Originator: Frank Hörtnagl / PD-KL Approved: Werner Körner / TE	Document:      DB0151005EN	page 1 of 1
--	----------------------------	-------------