


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SR-M</b>	52106610 14.11.2013

Reliable bending and anti-kink protection  
 High strain relief  
 Robust  
 For cables with large outer diameters  
 High degree of protection



Mechanical resistance



Optimum strain relief

### Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1

Handheld device  
 Portable equipment  
 Building sites  
 Moving machine parts

### Design

Metric connection thread acc. to EN 50262

### Note

Counter nut to be used: SKINDICHT® SM-M  
 For EMC version, refer to SKINDICHT® SRE-M  
 Example description: SR-M 12/7/512 = metric connection thread7 = PG function thread5 = clear opening of seal

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SR-M	1 / 3
--------------------	---------------------------	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SR-M</b>	<b>52106610</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	50 x 1,5
Clamping range ØF (mm):	32 - 38
Max. fitting size for installation (mm):	75
Function thread PG:	42
SW1/SW2 mm:	57 / 57
Overall length, C (mm):	111
Thread length, D (mm):	9
Clear opening F (mm):	38
Pieces / PU:	5
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Metal parts: nickel-plated brass O-ring: NBR Anti-kink protection: CR/NBR
Protection rating:	IP 65
Temperature range:	-20°C to +80°C

Product Management	Document: SKINDICHT® SR-M	2 / 3
--------------------	---------------------------	-------

U.I. Lapp GmbH	<h1>DATASHEET</h1>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SR-M</b>	<b>52106610</b> <b>14.11.2013</b>



Product Management	Document: SKINDICHT® SR-M	3 / 3
--------------------	---------------------------	-------