

U.I. Lapp GmbH	<h1>DATASHEET</h1>	
	<b>SKINTOP® KR-M ATEX plus</b>	54115265 04.04.2014


For the benefits, refer to SKINTOP® K-M ATEX plus



Mechanical resistance



Oil & Gas



Optimum strain relief



Reliability



Variety of approval certifications

### Application range

With reducing seal insert, to seal cables with smaller outer diameters.

### Design

Metric connection thread acc. to EN 50262

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINTOP® KR-M ATEX plus	1 / 2
--------------------	-----------------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINTOP® KR-M ATEX plus</b>	54115265 04.04.2014

### Technical Data

Article designation / size:	KR-M 50 ATEX plus
Clamping range ØF (mm):	22-29
Thread M:	50 x 1.5
SW (mm):	55
Overall length, C (mm):	54 - 62
Thread length, D (mm):	12
Pieces / PU:	5
Caution:	Refer to the instruction leaflet for the installation dimensions and torques
Approvals:	CE 0637 Ex II 2G Ex eb IIC Ex II 1D Ex ta IIIC IECEX IBE 13.0027X
Colour delivered:	RAL 9005 black/UV-resistant
Material:	Body: special polyamide Seal: special elastomer O-ring: CR
Tests:	DIN EN 60079-0 DIN EN 60079-7
Protection rating:	IP 68 - 10 bar
Temperature range:	-20°C to +80°C

Product Management	Document: SKINTOP® KR-M ATEX plus	2 / 2
--------------------	-----------------------------------	-------