



U.I. Lapp GmbH	<b>DATASHEET</b>	
	<b>SKINDICHT® SR</b>	52001230 14.11.2013

Reliable bending and anti-kink protection  
 High strain relief  
 Robust  
 For cables with large outer diameters  
 High degree of protection



Wide clamping range



Optimum strain relief



Robust

#### Application range

Cables for electrical appliances and machinery that are moved under normal use must be protected against excessive bending as required in accordance with VDE 0700-1

Handheld device  
 Portable equipment  
 Building sites  
 Moving machine parts

#### Design

PG connection thread

#### Note

Counter nut to be used: SKINDICHT® SM  
 For EMC version, refer to SKINDICHT® SRE

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Product Management	Document: SKINDICHT® SR	1 / 3
--------------------	-------------------------	-------


U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SR</b>	<b>52001230</b> <b>14.11.2013</b>

### Technical Data

Article designation / size:	SR 48/44
Clamping range ØF (mm):	40 - 44
Max. fitting size for installation (mm):	83
SW1/SW2 mm:	64 / 64
Overall length, C (mm):	119
Thread length, D (mm):	10
Pieces / PU:	1
Caution:	The installation dimensions can be found in appendix T21
On request:	Available with long connection thread
Material:	Body: nickel-plated brass O-ring: NBR Anti-kink protection: CR
Protection rating:	IP 65
Temperature range:	-20°C to +80°C

Product Management	Document: SKINDICHT® SR	2 / 3
--------------------	-------------------------	-------

U.I. Lapp GmbH	<b>DATASHEET</b>	 <b>LAPP GROUP</b>
	<b>SKINDICHT® SR</b>	52001230 14.11.2013



Product Management	Document: SKINDICHT® SR	3 / 3
--------------------	-------------------------	-------