



VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

“For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft’s success.”

BS-9.8 mm / 20 m VGA FLEX CAMERA

Nº 1209064

CE

VERSION 10/14

The camera serves as an attachment for endoscopes (not included). The camera can be used for optical troubleshooting or inspection at facilities and installations that do not carry a live voltage such as piping. Four LEDs allow for use in completely dark areas. It is waterproof (IP67); and a reel included ensures that the camera and camera neck can be stored safely. The goose neck allows the camera be inserted into hard to access areas. Power is supplied via the connected endoscope.

HIGHLIGHTS

9.8 mm camera head //

20 m flexible cable //

2 m extension cable //

Waterproof IP67 //

Belt-attachable cable reel //



TECHNICAL DATA

Compatible endoscopes	Item no. 123325, 123326, 123329, 123330, 123334, 283973, 513299, 513301, 1209851, 1086336
Camera-Ø	9.8 mm
Camera neck	20 m ± 2 cm
Endoscope extension cable	2 m ± 2 cm
Depth of field	6 cm - ∞
Field of view	54 °
Resolution	640 x 480 Pixels (VGA)
White balance	Automatic
Exposure	Automatic
Illuminant	4 LEDs (white)
Illuminance	max. 800 ± 150 lx (at a distance of 20 mm);
Bending radius	> 45 cm
Operating conditions	0 to +45 °C, 15 - 85 % RH (non-condensing)
Storage conditions	-10 to +50 °C, 15 - 85 % RH (non-condensing)
Protection type	IP67 (camera, camera neck)
Weight	approx. 1.34 kg

PACKAGE CONTENT

Flex camera (20 m) // Extension cable (2 m) // 2 x guide caps (Ø 1.5 cm, Ø 2.5 cm) // Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited.
This publication represent the technical status at the time of printing.