





ME030-508



: Poles  
 508 : Pitch 5.08mm  
 030 : Standard  
 ME : Type

PCB Layout



All materials are lead free according to EU.

Pitch : 5.08mm(0.200inch)					
Poles	A(mm)	A(inch)	Poles	A(mm)	A(inch)
2	11.76	0.463	15	77.80	3.063
3	16.84	0.663	16	82.88	3.263
4	21.92	0.863	17	87.96	3.463
5	27.00	1.063	18	93.04	3.663
6	32.08	1.263	19	98.12	3.863
7	37.16	1.463	20	103.20	4.063
8	42.24	1.663	21	108.28	4.263
9	47.32	1.863	22	113.36	4.463
10	52.40	2.063	23	118.44	4.663
11	57.48	2.263	24	123.52	4.863
12	62.56	2.463	25	128.60	5.063
13	67.64	2.663			
14	72.72	2.863			

Current rating : 16Amp AC300V  
 Insulation withstands volt : AC2000V min  
 Insulation resistance : >2000MΩ DC500V  
 Operation temperature : -40°C to +105°C

CONFIRMED & ACCEPTED BY

1	Material	Plating/Finish	Remark
2	Insulating body	Polyamide 66(UL94V-0)	Green
	Solder pin	Brass	Tin plated

DECA

PART NO.	ME030-508	VERSION	C	CONFIRMED BY	<i>Wizdom R</i>
SHEET OF	2/2	METRIC	MM	DRAWN BY	<i>Sing</i>
				DATE	2005/04/07
				GENERAL MANAGER	<i>J. L. G.</i>

版本 : A 版

Distributed by Conrad Electronic