




NdFeB-Magnet Rectangular N35 w/ Countersink Hole (2 PCS Pair)

Version 08/14

Item no. 1218980 / 1218981 / 1218982 / 1218983 / 1218984
/ 1218985 / 1218986 / 1218987 / 1218988 / 1218989 /
1218990 / 1218991 / 1218992 / 1218993



Dimension

Item no.	Length (A)	Width (B)	Height (C)	Countersink	Head Ø (D)	Base Screw Ø (E)	Head Height (F)
1218980	10mm	10mm	3mm	M3	6mm	3mm	1.5mm
1218981	10mm	10mm	5mm	M3	6mm	3mm	1.5mm
1218982	15mm	15mm	3mm	M4	8mm	4mm	2mm
1218983	15mm	15mm	5mm	M4	8mm	4mm	2mm
1218984	20mm	12mm	3mm	M4	8mm	4mm	2mm
1218985	20mm	12mm	5mm	M4	8mm	4mm	2mm
1218986	20mm	20mm	3mm	M4	8mm	4mm	2mm
1218987	20mm	20mm	5mm	M4	8mm	4mm	2mm
1218988	25mm	25mm	3mm	M5	10mm	5mm	2.5mm
1218989	25mm	25mm	5mm	M5	10mm	5mm	2.5mm
1218990	30mm	15mm	3mm	M5	10mm	5mm	2.5mm
1218991	30mm	15mm	5mm	M5	10mm	5mm	2.5mm
1218992	30mm	20mm	3mm	M5	10mm	5mm	2.5mm
1218993	30mm	20mm	5mm	M5	10mm	5mm	2.5mm

Grade N35
 Remanence Br 11.8 to 12.4 kGs
 Coercivity bHc ≥ 10.9 kOe
 Intrinsic Coercivity iHc ≥ 12 kOe
 Max Energy Product BHmax 33 to 37 MGOe
 Operating Temperature max. 80°C
 Tolerance ± 0.1 mm



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2013 by Conrad Electronic SE.